



BUILT FOR SMALL AND MEDIUM PROJECTS



High-end residential



Multi-residential



Restaurant




Hospitality



Shop

Up to 200 light points



EASY COMMISSIONING

Complicated wiring is now a thing of the past. Save time with the WiZ Pro Setup app for direct effortless and wireless commissioning, even when on-site Wi-Fi is not installed yet.



LOCAL WIRELESS CONTROL


Once you have the lights up and running, anyone can enjoy simple control via local accessories such as WiZ Pro remotes and sensors.

CONNECTED LIGHTING FOR WELCOMING SPACES


Turning any application into a warm and inviting environment for guests, clients and home owners has become one of the key features that businesses look for in a connected lighting package. Now all this and more is available in one affordable turnkey solution enabling ambience creation – WiZ Pro.

Transform your own lighting into connected fixtures with WiZ Pro bridge boxes and customizable modules or choose between a wide range of lamps and accessories to market under your own brand. Opt for reliable everyday connectivity that caters to the needs of all stakeholders with the WiZ platform.

Enjoy the variety of connected lighting benefits:




Easy local and remote control of your lights



Various light scenes to fit your application



Automate lights for better energy efficiency



APP CONTROL

Once the lighting installation is connected to Wi-Fi, end users can control the lights from anywhere with the WiZ app. Customize your lighting to fit your application or choose between a variety of pre-designed light modes for a rich experience.



ADVANCED FACILITIES MANAGEMENT


WiZ Pro Dashboard goes even further by allowing (multiple) lighting installation(s) control and remote site management. Get actionable light insights and monitoring with a clear overview of the entire installation, once it's connected to Wi-Fi.

A SOFTWARE SOLUTION FOR EACH STAKEHOLDER

Enjoy hassle-free wireless installation and local control with the WiZ app, as well as full control with cloud connectivity with WiZ Pro Setup app and WiZ Pro Dashboard. Enable a solution for each stakeholder with the WiZ Pro software suite that comes embedded within your WiZ Pro hardware.


WiZ PRO SETUP APP

WiZ Pro is plug-and-play, so basic set up is easy with the WiZ Pro Setup app through wireless direct commissioning, no gateway or Wi-Fi needed. Follow the step-by-step instructions on screen: add your products, decide which room you want them to be in and perform tests to make sure they work before you hand it over. Wireless accessories ensure easy, local control for everyday connectivity.



WiZ APP

Be a lighting designer, mix and match light modes or enjoy pre-defined Scenes to create the perfect ambience - to enhance the shopping experience or to entertain clients and friends when they come and visit. Discover the special human-centric lighting feature - Circadian Rhythm - which offers a smooth transition from cool white early in the cycle to warm white later on.



WiZ PRO DASHBOARD

Get the full picture and visualize where your lights are located within a space once you upload the area's floor plan. Set and supervise remotely the status of your lights and devices in any and all the locations you're managing. Each light's usage will be reported, including their remaining lifespan for predictive maintenance.



CREATE YOUR OWN WELCOMING SPACE. GET IN TOUCH WITH US TODAY.

WiZ Pro is an innovative new way to turn your OEM lighting products into smart solutions that create warm and comfortable ambiances. To know more about WiZ Pro and get in touch with a local representative, access wizconnected.com/en-us/business/pro.

BRING YOUR PRODUCTS ONTO THE WiZ PLATFORM

Choose from a wide range of WiZ Pro bridge boxes, lamps, luminaires, and accessories. If you want your own WiZ Pro products, our team will work with you to create a tailor-made solution. More WiZ Pro hardware products will be coming soon.



BRIDGE BOXES

Product name	12NC	Size mm	Dimming range %	Dimming method	Input voltage V	No. of channels	Life time h	Case qty pcs
WiZ Pro DW Bridge Box B 12-24V	929002686103	88x41x28	5-100	PWM	12-24 VDC	1	50000	40
WiZ Pro TW Bridge Box B 12-24V	929002686003	88x41x28	5-100	PWM	12-24 VDC	2	50000	40
WiZ Pro RGBTW Bridge Box B 12-24V	929002685903	88x41x28	5-100	PWM	12-24 VDC	5	50000	40

LAMPS

Product name	12NC	Type	Base	Shape	Power W	White CCT range K	Flux lm	CRI Ra	Life time h	Case qty pcs
WiZ Pro A19 E26 TW 8.8W 120V	929002383173	Standard	E26	A19	8.8	2700-6500	800	90	25000	6
WiZ Pro A19 E26 RGBTW 8.8W 120V	929002383373	Standard	E26	A19	8.8	2200-6500	800	90	25000	6
WiZ Pro A21 E26 TW 14.5W 120V	929002449273	Standard	E26	A21	14.5	2700-6500	1600	90	15000	6
WiZ Pro A21 E26 RGBTW 14.5W 120V	929002449373	Standard	E26	A21	14.5	2200-6500	1600	90	15000	6
WiZ Pro B12 E12 TW 3.9W 120V	929002447573	Standard	E12	B12	3.9	2700-6500	355	90	15000	6
WiZ Pro B12 E12 RGBTW 3.9W 120V	929002447673	Standard	E12	B12	3.9	2200-6500	355	90	15000	6
WiZ Pro BR30 E26 TW 7.2W 120V	929002383273	Standard	E26	BR30	7.2	2700-6500	650	90	25000	6
WiZ Pro BR30 E26 RGBTW 7.2W 120V	929002383473	Standard	E26	BR30	7.2	2200-6500	650	90	25000	6
WiZ Pro PAR16 GU10 TW 4.9W 120V	929002447173	Standard	GU10	PAR16	4.9	2700-6500	400	90	25000	6
WiZ Pro PAR16 GU10 RGBTW 4.9W 120V	929002447273	Standard	GU10	PAR16	4.9	2200-6500	400	90	25000	6
WiZ Pro PAR38 E26 TW 13W 120V	929002447973	Standard	E26	PAR38	13	2700-6500	1200	90	25000	6
WiZ Pro PAR38 E26 RGBTW 13W 120V	929002448073	Standard	E26	PAR38	13	2200-6500	1200	90	25000	6
WiZ Pro FL CL A19 E26 TW 7W 120V	929003009673	Vintage/ Filament	E26	A19	7	2700-5000	800	90	15000	6
WiZ Pro FL CL ST19 E26 TW 5.5W 120V	929003009773	Vintage/ Filament	E26	ST19	5.5	2700-5000	500	90	15000	6
WiZ Pro FL CL G25 E26 TW 5.5W 120V	929003009873	Vintage/ Filament	E26	G25	5.5	2700-5000	500	90	15000	6
WiZ Pro FL CL BA11 E12 TW 3.8W 120V	929003009173	Vintage/ Filament	E12	BA11	3.8	2700-5000	350	90	15000	6
WiZ Pro FL CL B11 E12 TW 3.8W 120V	929003009373	Vintage/ Filament	E12	B11	3.8	2700-5000	350	90	15000	6

STRIPS

Product name	12NC	Input voltage	Cord length m/ ft.	Power W	White CCT range K	Flux lm	CRI Ra	Life time h	Case qty pcs
WiZ Pro LED Strip RGBTW 2M Kit-A	929002681373	100-120 VAC	1.5/ 4.9	20	2700-6500	1600	80	15000	6
WiZ Pro LED Strip RGBTW 1M Ext-2	929002681473	12 VDC	N/A	11	2700-6500	800	80	15000	6

LUMINAIRES

Product name	12NC	Size In.	Size mm	Power W	White CCT range K	Flux lm	CRI Ra	Life time h	Case qty pcs
WiZ Pro RDL6 TW 8.3W 120V	929003081673	6	188x70	8.3	2700-6500	750	90	25000	6
WiZ Pro RDL6 RGBTW 12.5W 120V	929002617873	6	188x70	12.5	2700-6500	1150	90	25000	6

ACCESSORIES

Product name	12NC	Power source	Control range m/ ft.	Detection range m/ ft.	Battery life hrs	Case qty pcs
WiZ Pro Remote Control US	929002551273	2 X LR03 AAA, Alkaline Zn-MnO2	15/ 49	N/A	1	6
WiZ Pro Wireless Sensor w/batteries US	929002424873	2 X LR6 AA, Alkaline Zn-MnO2	15/ 49	Height: 3 Beam Angle: 120°	1	6

MODULES

WiZ Pro modules are designed to fit your custom product specifications. Operating on Wi-Fi + Bluetooth standard protocols, the modules enable the wireless IoT benefits brought by the WiZ Pro smart lighting platform, as well as ease of installation and scalability. Due to their small size, you have the flexibility to integrate them in a range of luminaire designs. Enabling various dynamic light scenes with Tunable White and a variation of colors, the WiZ Pro modules cater to the needs of any application. To find out how you can benefit from integrating WiZ Pro modules into your products, please contact the WiZ team via wizconnected.com/en-us/business/pro.