

Xitanium SR

LED Driver

by (Signify

XI040C110V054VPT2



The Xitanium SR LED driver can help reduce complexity and cost of light fixtures used in wireless connected lighting systems. It features a standard digital interface to enable direct connection to any suitably qualified RF sensor on the market. Functionality is integrated into the SR driver that ordinarily would require additional auxiliary components. The result is a simpler, less expensive light fixture that can enable every fixture to become a wireless node.


Specifications


Input Volt. (Vac)	Out- put Pow- er (W)	Output Voltage (V)	Out- put Cur- rent (A)	Efficiency @ Max Load and 75°C Case	Max Case Temp. (°C)	Input Cur- rent (A)	Max. Input Pow- er (W)	THD @ Max Load (%)	Power Factor @ Max Load	Surge Protect. (Ring Wave, KV)	Envir. Pro- tect. Rating	Dim.	Dim. Range	Min. Output Cur- rent (A)	Driver Type	Other Comments
120	40	16 - 54 Class 2	0.1 - 1.1	85	Life- 75°C	0.4	47	<10%	>0.95	2.5	UL damp	SR	1% ~	0.0025	Constant	SR input current
277	Output		87	UL- 85°C	0.18	''	<15%		2.0	& dry		100%	0.0023	Current	(PSU off), max 2mA	

Enclosure

	In. (mm)
Case Length	14.17 (360)
Case Width	1.18 (30)
Case Height	1.0 (25.4)
Mounting Length	13.78 (350)

Wiring Diagram





Both output positive and negative connectors are equivalent (same electrical point).

Connect wires:

Use 18 AWG Solid Copper Wire Rated>=300V. Strip Wire 3/8".

Warning

- Install in accordance with national and local electrical codes.
- The field-wiring leads or push-in terminals shall be fully enclosed.









40W 1.1A 54V (1% dim) with SimpleSet

Features

- Standard digital interface based on proposed ANSI C137.4
- Auxiliary power for sensors through digital connection, default "on" for connection to single sensing/RF device
- Energy metering and advanced diagnostics
- $\boldsymbol{\cdot}$ Continuous dimming down to 1%
- Low standby power <0.25W with no loading and <0.5W with 0.15W load
- Drive current setting via SimpleSet wireless programming
- · 5-year limited warranty*

Benefits

- Enable interoperability with diverse wireless sensors/network systems
- Reduce complexity and cost of fixture by eliminating auxiliary components ordinarily required for powering sensors, switching fixture off and monitoring energy use
- Future proof through standard interface to any suitable sensor and ease of adjustable drive current

Application

Indoor linear applications such as troffers and pendants

Product Data

All specifications are typical and at 25°C Tcase unless otherwise specified.

Ordering Information						
Order Code	XIO40C110V054VPT2 (12NC:929001748613)					
Full Product Code	XIO40C110V054VPT2M (Mid-pack, 18/box)					
Full Product Name	Xitanium 40W 0.10-1.1A 54V INT SR					
Global Trade Identification Number (GTIN)	781087158043					
Input Information						
Inrush Current	Per NEMA 410					
Line Voltage (AC Operation)	120-277VAC +/- 10%					
Line Frequency	50/60Hz					
Output Information						
Output Voltage Range	16 - 54V					
Output Current Ripple	<15% at max lout (ripple = pk-avg/avg) Low frequency (<120 Hz) content <5%					
Output Current Tolerance	±5% at max output current					
Open Circuit Voltage	60V					
Protections	Short Circuit and Open Circuit Protection for LED + and LED-					
	The dimming lead leakage current is 0.01mA. The maximum number of drivers that can be connected in parallel to one dimming control circuit is based on this dimming lead leakage current and the calculation is described in the corresponding Design-in Guide.					
Features						
AOC (Adjustable Output Current)	100mA to 1100mA via SimpleSet programming					
Life @ TC 75°C	50000 hr [nom] (refer to graphs)					
Suitable for Outdoor Use?	No					
Interfaces	AOC (SimpleSet), SR					
Ambient Temp Range	-20°C to +50°C					
Max Case Temperature (Tcase)	85°C for UL, 75°C for life					
Earth Leakage Current	0.75 mA [max]					
THD Total	Refer to graph					
Power Factor	Refer to graph					
Sensor Power Supply	52-60mA Peak (55mA typ.); 12vdc-20vdc (14vdc typ.) (refer to graph)					
Power Reporting Accuracy	±0.5W/±4%					
Environment & Approbation						
Agency Approbations	UL8750, UL1310, cUL, Class P (UL, cUL)					
Audible Noise	<24dB Class A					
Isolation Between Output and Input	Refer to table (page 8)					
Isolation of Controls	Refer to table (page 8)					
EMC (Electromagnetic Compliance)	Meets FCC 47 Part 15 Class A					
Envir. Protection Rating	UL Dry & Damp					
Net Weight Per Piece	0.58 Lbs / 0.265 Kgs					


40W 1.1A 54V (1% dim) with SimpleSet


Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Dimming Characteristics

Dimming is accomplished through the 2-wire DALI connection to the sensor. DALI standard IEC62386_102 Edition 2 defines the logarithmic dimming curve. DALI standard IEC62386_107 Edition 1 defines the linear dimming curve as well as the command for switching between logarithmic and linear curves (Default = Logarithmic).






40W 1.1A 54V (1% dim) with SimpleSet

Electrical Specifications


All the specifications are typical and at 25°C Tcase unless specified otherwise.

SR Power Supply Characteristics (Typical)



Note:

Power supply through digital connection, default "on," for connection of one driver to one sensing/RF device. Consult your representative for use with multiple devices.



Note:


For 1% dimming output current setting through AOC should be >0.25A.

40W 1.1A 54V (1% dim) with SimpleSet


Performance Characteristics

Based on measurements on a typical sample at 75°C case. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification.

Power Factor vs. Output Power



Total Harmonic Distortion vs. Output Power




40W 1.1A 54V (1% dim) with SimpleSet

Performance Characteristics


Based on measurements on a typical sample. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification.

Output Current Vs. Driver Case Temperature



Note: There is $\pm 5^{\circ}$ C tolerance on the driver case temperature

Driver Lifetime vs. Driver Case Temperature




40W 1.1A 54V (1% dim) with SimpleSet


Performance Characteristics

Based on measurements on a typical sample. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification.

Efficiency Vs. Output Voltage at 120Vac




Efficiency Vs. Output Voltage at 277Vac



40W 1.1A 54V (1% dim) with SimpleSet

Inrush Current Info



Vin	Ipeak	T (@ 10% of Ipeak)		
120 Vrms	2.7 A	36 µs		
277 Vrms	9.8 A	28 µs		

Lightning Surge Info

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)		
100 kHz Ring Wave (w/t 30 ₂)	>2.5kV	>2.5kV		

Isolation:

Isolation	Input Connectors	Output + AOC	SR Connectors	Chassis	
Input Connectors	_	1600V	2500V	1600V	
Output + AOC	1600V	-	500V	500V	
SR Connectors	2500V	500V	-	500V	
Chassis	1600V	500V	500V	-	

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners