













Find what you need, right now!

Use the table below to find the product most commonly used for the given application. Don't see what you need? Visit www.bodine.com for a complete selection. Call 1-888-BODINE-8 or email bodinetech@signify.com if you need help.

	Order Code (Click for product page)	
Combo Exit Signs – FirstLink Connected		
 Red lettering, white housing, up to 76' spacing	BCA2RWFL1	
 Green lettering, white housing, up to 76' spacing	BCA2GWFL1	
Exit Signs – FirstLink Connected		
 Red lettering, white housing, single or double faced	BXARWFL1	
 Green lettering, white housing, single or double faced	BXAGWFL1	
Unit Equipment – FirstLink Connected		
 2 Head, LED, 180 lumens, up to 40' spacing	BUA1WFL1	
 2 Head, LED, 520 lumens, up to 76' spacing	BUA2WFL1	
For LED Center Basket Troffers, LED Strip fixtures:		
Installed inside fixture:		
 10 W EM driver, Class 2 output, linear, FirstLink connected	BSL10T4UAK55PKFLI2	
10 W EM driver, Class 2 output, linear, selectable self-test	BSL10T3UAK55PKI2	
10VA inverter, up to 50VA w/0-10V dim load	ELIS10	
Installed outside of or remote from fixture:		
14 W EM driver, Class 2 output w/conduit (14W)	BSL14B2UAK55C1I1	
10 W EM driver, Class 2 w/conduit	BSL310C2WM	
10VA inverter w/conduit, up to 50VA w/0-10V dim load	ELIS10C	
For LED Panels:		
10 W EM driver, Class 2 w/conduit	BSL310C2WM	
10VA inverter w/conduit, up to 50VA w/0-10V dim load	ELIS10C	
25VA inverter w/conduit, up to 200 W w/0-10V dim load	ELIS25J1UK50C1AD11	
For LED HighBays:		
25VA inverter w/conduit, up to 200 W w/0-10V dim load	ELIS25J1UK50C1AD11	

Distributor Quick Reference

For Retrofit, Type B TLEDs:

1000 Lumens Kit (driver+LED module)	BLK1000T3UK55TS1
25VA inverter w/conduit, up to 200 W w/0-10V dim load	ELIS25J1UK50C1AD11
12 W inverter, for <u>phase cut dimmable</u> TLEDs up to 15 W	BTB15D



For Retrofit, Type A TLEDs:

1000 Lumens Kit (driver+LED module)	BLK1000T3UK55TS1
1 lamp, linear, up to 16.5 W	B50CT



For LED Downlights:

10VA inverter w/conduit, up to 50VA w/0-10V dim load	ELIS10C
6 W Class 2 output, bottom stud mount	BSL06M5UAK55BSI1



For Fluorescent troffers:

1 or 2 lamps, T5, T8, 4-pin compact, 1400 lumens max	B50
1 lamp, 18-42 W 4-pin CFL, 750 lumens max	B94CGUM



Emergency Lighting Mini-Inverters – Useful for providing high emergency power to large or multiple luminaires.

100VA output, 120-277VAC in/out, up to 400VA w/0-10V dim load	ELIS100
250VA output, 120-277VAC in/out, up to 800VA w/0-10V dim load	ELIS250I2UO30ADI2
400VA output, 120-277VAC in/out	ELIS400CEC
400VA output, 120-277VAC in/out, up to 800VA w/0-10V dim load	ELIS400I2UO30ADI2



Products marked with the FirstLink logo have Bodine's FirstLink capabilities.

Though fully functional self-testing emergency lighting products on their own, connecting these products to the free FirstLink application allows for all test data to be wirelessly collected. The FirstLink application also allow you to control your emergency lights, like initiating a test manually and changing the testing time and date. Visit www.bodine.com/firstlink for more.

Not finding what you need? Contact us!

For a broader range of products, including extended runtime, high voltage, and for cold temperature applications, find them on the web at www.bodine.com, or, contact Bodine's support team.

Call or e-mail: 1-888-BODINE-8 / Bodinetech@Signify.com

