

bodine

Emergency Ballast

Linear fluorescent

B50CT



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Emergency ballast for Fluorescent and
Type A TLED lamps
Meets CEC Title 20 efficiency standards

Product order number: B50CT
12 NC number: 913702469601

Specifications

UL Listed For US And Canada

Factory or Field Installation
(Indoor and Damp)

Illumination Time

90 Minutes

Initial Light Output

Up to 1400 Lumens

Full Warranty

5 Years (NOT pro-rata)

Universal Input Voltage

120 Through 277 VAC, 50 or 60 Hz

AC Input Current

60 mA

AC Input Power Rating

5.0 Watts

Test Switch

2W-ITS (2-wire Illuminated Test Switch)

Battery

High-Temperature, Maintenance-Free
Nickel-Cadmium Battery
7- to 10-Year Life Expectancy

Battery Charging Current

180 mA

Recharge Time

24 Hours

Charging Indicator Light

LED

Temperature Rating (Ambient)

0°C to +50°C (32°F to 122°F)

Dimensions

13.31" x 2.20" x 1.18"
(338.07 mm x 55.88 mm x 29.97 mm)
Mounting Center 12.79" (325 mm)

Weight

2.78 lbs. (1.26 kg)



Benefits:

- Compatible with 7 - 16.5W Type A TLED lamps (including LED T8 InstantFit)
- Meets CEC Title 20 efficiency standards
- Low profile case (1.18"H)
- Universal Input (120 through 277 VAC, 50/60Hz)

Dimensions

13.31" x 2.20" x 1.18"

Mounting Center 12.79"



An illuminated test switch/charging indicator light is provided.

B50CT Emergency ballast for fluorescent and TLED lamps

Application

The B50CT emergency ballast works in conjunction with an AC ballast to convert new or existing fluorescent or TLED fixtures into emergency lighting. The emergency ballast handles a wide range of input voltages and frequencies and consists of a high-temperature nickel-cadmium battery, charger and electronic circuitry in one compact metal case. B50CT operates one lamp in emergency mode (see Table 1). It is compatible with most single- and multi-lamp electronic and dimming AC ballasts. If used in an emergency-only fixture, no AC ballast is necessary. The B50CT is suitable for indoor and damp locations and for sealed & gasketed fixtures, including fixtures rated for wet locations. It is not suitable for air handling heated air outlets or wet or hazardous locations. For information about specific lamp and ballast compatibility, please call the factory. Recommended applications include: international line voltages from 120 through 277 VAC (50 or 60 Hz); drilling rigs where generators are the primary source of power; and other applications requiring higher tolerance of line voltage variation or harmonic distortion.

Operation

When AC power fails, the B50CT immediately switches to the emergency mode, operating one lamp at a reduced lumen output for a minimum of 90 minutes. When the AC power is restored, the emergency ballast automatically returns to the charging mode and, using a patented circuit, delays AC ballast operation for approximately three seconds to prevent false tripping of the AC ballast end-of-lamp-life shutdown circuits.

Installation

The B50CT does not affect normal fixture operation and may be used with either a switched or unswitched fixture. If a switched fixture is used, an unswitched hot lead must be connected to the emergency ballast. The emergency ballast must be fed from the same branch circuit as the AC ballast. The B50CT may be installed inside, on top of or remote from the fixture. The emergency ballast may be remotely installed up to half the distance the AC ballast manufacturer recommends removing the AC ballast from the lamp or up to 50 feet, whichever is less. Installation is not recommended with fixtures where the ambient temperature may fall below 0°C.

Emergency Illumination

Depending on the wattage and lamp selected, the B50CT produces up to 1400 lumens initial emergency light output (see Table 2).

Specification

Emergency lighting shall be provided by using a fluorescent or TLED fixture equipped with a Bodine B50CT emergency ballast. This emergency ballast shall consist of a high-temperature, maintenance-free nickel-cadmium battery, charger and electronic circuitry contained in one 13.31" x 2.2" x 1.18" metal case. A solid-state charging indicator light to monitor the charger and battery, a 2-wire illuminated test switch and installation hardware shall be provided. The emergency ballast, using a patented circuit, shall delay AC ballast operation for approximately three seconds to prevent false tripping of AC ballast end-of-lamp-life shutdown

circuits. The emergency ballast shall be capable of operating [one] _____ lamp (see Table 1) at _____ lumens (see Table 2) initial light output in the emergency mode for a minimum of 90 minutes. It shall be suitable for indoor and damp locations and for sealed & gasketed fixtures, including fixtures rated for wet locations. The B50CT shall operate at any line voltage from 120 through 277 VAC at frequencies of 50 or 60 Hz. The B50CT shall have 5.0 Watts of input power and shall exceed emergency standards set forth by the current NEC and meets Title 20 CEC (California Energy Commission) standards. The emergency ballast shall be UL Listed for factory or field installation inside, on top of or remote from the fixture.

Warranty

Model B50CT is warranted for five (5) full years from date of purchase. Please see detailed warranty information on our web site.

Table 1 Lamp Compatibility

| LAMP (DIAMETER) | BASE TYPE | WATTAGE (Length) | NO. of LAMPS (EMERGENCY) |
|---|------------------------|----------------------|--------------------------|
| (1", 1¼", 1½") T8, T12 | Single or Bipin | 17 - 40 W (2'-4') | 1 |
| LONG COMPACT | 4-PIN (2G11) | 18 - 39 W | 1 |
| | | 40 - 55 W | 1 |
| TWIN/QUAD/TRIPLE TWIN-TUBE COMPACT | 4-PIN (G24q, Gx24q) | 13 - 42 W | 1 |
| T5 & T5 HO | MINIATURE BIPIN | 14 - 54 W (2'-4') | 1 |
| | HO CIRCLINE | 22 - 55 W | 1 |
| Type A TLED lamps (including Philips LED T8 InstantFit) | Bipin | 7 - 16.5 W | 1 |

Table 2 Initial Lumen Output

| LAMP | LUMENS |
|----------------------|--------|
| F54T5/HO | 1400 |
| 1x F32T8 | 1130 |
| TL5C22W/840 Circline | 730 |
| TL5C55W/840 Circline | 985 |
| PL-L 40W/830/4P | 1190 |
| PL-L 55W/840/4P | 1220 |
| TLED T8 16.5W | 1140 |

