

ADVANCE

by (s) ignify

Centium T5


Ballasts

ICN2S39N

Electrical Specifications at 120V

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (F/C)	Input Current (Amps)	Input Power (ANSI Watts)	Ballast Factor	MAX THD %	Power Factor	MAX Lamp Current Crest Factor	B.E.F.
(1) FC9T5 & (1) FC12T5	2	62	0/-18	0.56	66	0.95	10	0.97	1.7	1.44
F24T5/HO	1	24	0/-18	0.25	30	1.14	15	0.97	1.7	3.80
F24T5/HO	2	24	0/-18	0.49	59	1.15	10	0.97	1.7	1.95
F39T5/HO	1	39	0/-18	0.36	43	1.01	10	0.97	1.7	2.35
* F39T5/HO	2	39	0/-18	0.71	85	0.99	10	0.97	1.7	1.16
FC12T5	1	40	0/-18	0.38	45	1.03	10	0.97	1.7	2.29
FC12T5	2	40	0/-18	0.68	81	0.91	10	0.97	1.7	1.12
FC9T5	1	22	0/-18	0.24	29	1.10	15	0.97	1.7	3.79
FC9T5	2	22	0/-18	0.45	54	1.07	15	0.97	1.7	1.98
FT24W/2G11	1	24	0/-18	0.24	28	1.11	15	0.97	1.7	3.96
FT24W/2G11	2	24	0/-18	0.47	56	1.12	10	0.97	1.7	2.00
FT36W/2G11	1	36	0/-18	0.28	34	0.92	10	0.97	1.7	2.71
FT36W/2G11	2	36	0/-18	0.55	66	0.89	10	0.97	1.7	1.35
FT40W/2G11/RS	1	40	0/-18	0.37	45	0.99	10	0.97	1.7	2.20

Wiring Diagram



Diag. 74


The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

	in.	cm.
Black	24	61
White	24	61
Blue	27	68.6
Red	27	68.6
Yellow	47	119.4
Gray		0
Violet		0

	in.	cm.
Yellow/Blue		0
Blue/White		0
Brown		0
Orange		0
Orange/Black		0
Black/White		0
Red/White		0





Enclosure Dimensions

OverAll (L)	Width (W)	Height (H)	Mounting (M)
9.5 "	1.3 "	1.0 "	8.9 "
9 1/2	1 3/10	1	8 9/10
24.1 cm	3.3 cm	2.5 cm	22.6 cm







ICN2S39N@120V			
Brand Name	CENTIUM T5		
Ballast Type	Electronic		
Starting Method	Programmed Start		
Lamp Connection	Series		
Input Voltage	120-277		
Input Frequency	50/60 HZ		
Status	Active		

Electrical Specifications at 120V

Notes:

Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.
- 1.2 Ballast shall be provided with integral leads or poke-in wire trap connectors color-coded per ANSI C82.11.

Section II - Performance

- 2.1 Ballast shall be Programmed Start.
- 2.2 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.
- 2.3 Ballast shall operate from 50/60 Hz input source of ______ (120V through 277V or 347V through 480V) with sustained variations of +/- 10% (voltage and frequency).
- 2.4 Ballast shall be high frequency electronic type and operate lamps at a frequency above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.
- 2.5 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.6 Ballast shall have a minimum ballast factor of 1.0 for primary lamp application.
- 2.7 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.8 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage with primary lamp.
- 2.9 Ballast shall have a Class A sound rating.
- 2.10 Ballast shall have a minimum starting temperature of _____ {-18C (0F) or -29C (-20F)} for primary lamp. Consult lamp manufacturer for temperature versus light output characteristics.
- 2.11 Ballast shall provide Lamp EOL Protection Circuit.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.
- 2.13 Four-lamp ballast shall have (semi-independent or independent) lamp operation.

Section III - Regulatory

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with applicable requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, for Non-Consumer equipment.
- 3.6 Ballast shall comply with UL Type CC rating.
- 3.7 Ballast shall comply with NEMA 410 for in-rush current limits.


Section IV - Other

- 4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C. Ballasts with a "90C" designation in their catalog number shall also carry a three-year warranty at a maximum case temperature of 90C.
- 4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.



Electrical Specifications at 277V

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (\(\mathcal{F}/\mathcal{C}\))	Input Current (Amps)	Input Power (ANSI Watts)	Ballast Factor	MAX THD %	Power Factor	MAX Lamp Current Crest Factor	B.E.F.
(1) FC9T5 & (1) FC12T5	2	62	0/-18	0.24	66	0.94	10	0.97	1.7	1.42
F24T5/HO	1	24	0/-18	0.12	30	1.14	20	0.97	1.7	3.80
F24T5/HO	2	24	0/-18	0.22	58	1.14	10	0.97	1.7	1.97
F39T5/HO	1	39	0/-18	0.16	43	1.00	15	0.97	1.7	2.33
* F39T5/HO	2	39	0/-18	0.30	83	1.00	10	0.97	1.7	1.20
FC12T5	1	40	0/-18	0.17	45	1.03	15	0.97	1.7	2.29
FC12T5	2	40	0/-18	0.30	81	0.92	10	0.97	1.7	1.14
FC9T5	1	22	0/-18	0.11	29	1.09	20	0.97	1.7	3.76
FC9T5	2	22	0/-18	0.20	54	1.07	15	0.97	1.7	1.98
FT24W/2G11	1	24	0/-18	0.13	29	1.11	15	0.97	1.7	3.83
FT24W/2G11	2	24	0/-18	0.21	55	1.11	10	0.97	1.7	2.02
FT36W/2G11	1	36	0/-18	0.15	33	0.90	15	0.97	1.7	2.73
FT36W/2G11	2	36	0/-18	0.24	65	0.90	10	0.97	1.7	1.38
FT40W/2G11/RS	1	40	0/-18	0.17	45	0.99	15	0.97	1.7	2.20



Diag. 74


The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

	in.	cm.
Black	24	61
White	24	61
Blue	27	68.6
Red	27	68.6
Yellow	47	119.4
Gray		0
Violet		0

	in.	cm.
Yellow/Blue		0
Blue/White		0
Brown		0
Orange		0
Orange/Black		0
Black/White		0
Red/White		0





Enclosure Dimensions

OverAll (L)	Width (W)	Height (H)	Mounting (M)
9.5 "	1.3 "	1.0 "	8.9 "
9 1/2	1 3/10	1	8 9/10
24.1 cm	3.3 cm	2.5 cm	22.6 cm







ICN2S39N@277V			
Brand Name	CENTIUM T5		
Ballast Type	Electronic		
Starting Method	Programmed Start		
Lamp Connection	Series		
Input Voltage	120-277		
Input Frequency	50/60 HZ		
Status	Active		

Electrical Specifications at 277V

Notes:

Section I - Physical Characteristics

- 1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.
- 1.2 Ballast shall be provided with integral leads or poke-in wire trap connectors color-coded per ANSI C82.11.

Section II - Performance

- 2.1 Ballast shall be Programmed Start.
- 2.2 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.
- 2.3 Ballast shall operate from 50/60 Hz input source of ______ (120V through 277V or 347V through 480V) with sustained variations of +/- 10% (voltage and frequency).
- 2.4 Ballast shall be high frequency electronic type and operate lamps at a frequency above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.
- 2.5 Ballast shall have a Power Factor greater than 0.98 for primary lamp.
- 2.6 Ballast shall have a minimum ballast factor of 1.0 for primary lamp application.
- 2.7 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.
- 2.8 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage with primary lamp.
- 2.9 Ballast shall have a Class A sound rating.
- 2.10 Ballast shall have a minimum starting temperature of ______ {-18C (0F) or -29C (-20F)} for primary lamp. Consult lamp manufacturer for temperature versus light output characteristics.
- 2.11 Ballast shall provide Lamp EOL Protection Circuit.
- 2.12 Ballast shall tolerate sustained open circuit and short circuit output conditions.
- 2.13 Four-lamp ballast shall have (semi-independent or independent) lamp operation.

Section III - Regulatory

- 3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.
- 3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.
- 3.4 Ballast shall comply with ANSI C82.11 where applicable.
- 3.5 Ballast shall comply with applicable requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, for Non-Consumer equipment.
- 3.6 Ballast shall comply with UL Type CC rating.
- 3.7 Ballast shall comply with NEMA 410 for in-rush current limits.

Section IV - Other

- 4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.
- 4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C. Ballasts with a "90C" designation in their catalog number shall also carry a three-year warranty at a maximum case temperature of 90C.
- 4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.



 $The information\ presented\ in\ this\ document\ is\ not\ intended\ as\ any\ commercial\ offer\ and\ does\ not\ form\ part\ of\ any\ quotation\ or\ contract.$



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855–486–2216 signify Canada Ltd. 181 Hillmount Road, Markham, ON, Canada L6C 2S3 Jalenhone 800-668-9008