ADVANCE

by (signify

LED Driver

Xitanium SR

XJ180C180V144VSF2




The Advance Xitanium SR LED driver can help reduce complexity and cost of light fixtures used in connected lighting systems in outdoor lighting applications. It features a standard digital interface to enable direct connection to SR-certified components. Functionality that ordinarily would require additional auxiliary components is integrated into the driver. The result is a simple, cost-effective light fixture that can enable every fixture to become a wireless node.

Specifications

Input Voltage (Vrms)	Output Power (W)	Output Voltage (V)	Output Current (A)	Efficiency@ Max. Load and 70°C Case	Max. Case Temp. (°C)	Input Current (Arms)	Max. Input Power (W) ¹	THD @ Max. Load	Power Factor @ Max. Load	Surge Protection Common/ Diff (KV)	Envir. Protection Rating	Dim.	Dimming Range	Min. Output Current (A)	Driver Type
277	- 180	50 - 144	4 0.1A -1.8A	91.5	Life - 85°C	0.75 200	<10%	>0.95 6	in i	UL damp	DALL	10% ~ 100%	0.1	Constant Current	
480				93	UL - 90°C		<15%			& dry	DALI				

Enclosure

	In. (mm)	Tolerance
Case Length (L2)	8.31 (211.1)	± 0.5mm
Case Width (W)	2.31 (58.6)	± 0.5mm
Case Height (H)	1.48 (37.6)	± 0.5mm
Mounting Length (M)	8.91 (226.3)	± 0.5mm
Overall Length (L1)	9.45 (240.0)	± 0.5mm
Center of SimpleSet Antenna (L3)	3.75 (95.3)	± 0.5mm




1. Based on 1W load from SR power supply and 6.2W load from auxiliary power supply.

Warning

- Install in accordance with national and local electrical codes.
- The field-wiring leads or push-in terminals shall be enclosed.

Wiring Diagram

	Wire Length (mm)
Black/Orange (Line)	270 (± 30)
Black/White (Neutral)	270 (± 30)
Red (Positive, LED output)	270 (± 30)
Blue (Negative, LED output)	270 (± 30)
Violet/White (Positive, DA+)	270 (± 30)
Gray/White (Negative, DA-)	270 (± 30)
Brown(Positive +24V)	270 (± 30)
Orange(Logical Signal Input)	270 (± 30)





Electrical Specifications

All the specifications are typical and at 25°C Ta unless specified otherwise.

Features

- Compatible with SR-certified devices
- Standard SR digital interface including integral power supply
- Auxiliary power supply for higher power device requirements
- Accurate energy metering
- Logic signal input
- Drive current setting via SimpleSet
- 5-year limited warranty¹
- Memory Bank 1 extension per ANSI C137.4

Product Data

Benefits

- Enables interoperability with multiple sensor/network system vendors
- Reduces cost and complexity of outdoor connected lighting systems²
- Eliminates need for high-voltage relays to increase system reliability
- 2% metering accuracy meets proposed ANSI standard C136.52
- Can be used with standard motion sensors for local control to complement network control
- Standardized luminaire data for Asset Management

Application

- Site & area
- Parking garages
- Floodlights
- Roadway

Ordering Information					
Order Code	XJ180C180V144VSF2M (Mid-Pack, 10pcs/Box), 12NC: 929001792313				
GTIN	781087163740				
Input Information					
Line Frequency	50/60Hz				
Min. Mains Voltage Operational	250Vac				
Max. Mains Voltage Operational	528Vac				
Output Information					
Maximum Open Circuit Voltage	200Vdc				
Output Current Ripple = pk-Avg/Avg	<15% @ max lout				
Output Current Tolerance (At Maximum Output Current)	<5%				
Protections	Short Circuit and Open Circuit Protection for LED + and LED-				
Control Lead Leakage Current	The dimming lead leakage current is 0.031mA. The maximum number of drivers that can be connected in parallel to one dimming control circuit is based on this dimming lead leakage current and the calculation is described in the corresponding Design-in Guide.				
Features					
AOC (adjustable output current)	0.1A-1.25A via SimpleSet (Factory Default at 0.7A)				
CLO, Dynadimmer, Suitable for Outdoor Use? DTL (Advanced thermal control)?	Yes				
Interfaces	Simpleset, Sensor Ready(SR), Logical Signal Input (LSI), Auxilairy Power Supply				
Configurable Features	Advance Driver Thermal Limit, Dynadimmer, Dim to Off, password protection, and many others.				
Power Reporting Accuracy	+/-2% in performance window and under nominal operating conditions				
Auxiliary Power Supply (According to ANSI C137.4)					
Nominal Aux. Output Voltage	24Vdc (± 10%, including line and load regulation)				

 Advance Xitanium LED drivers are designed and manufactured to engineering standards correlating to an average life expectancy of 50,000 hours of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.

2. Functionality that ordinarily would require additional auxiliary components is integrated into the driver.

Electrical Specifications

All the specifications are typical and at 25°C Ta unless specified otherwise.

Product Data (continued)


3W continuous, 10.5W peak for 1.2ms		
Short Circuit & Open Circuit Protection for Aux. + and Aux. – and Over-temperature Foldback		
52mA to 60mA		
12V to 20V		
DALI-2, D4i, ANSI C137.4		
No		
Yes		
<3V or open		
>7V		
2mA		
-40°C to +55°C		
85°C for Life & 90°C for UL Safety		
UL 8750, cUL, Class P (UL, cUL)		
FCC Title 47 Part 15 Class A		
<24dB Class A		
2.1Lbs/0.95Kgs		
UL Dry and Damp		


Electrical Specifications

All specifications are typical and at 25°C Ta unless specified otherwise.

Dimming Characteristics

SR drivers use a logarithmic dimming curve as default. Dimming is accomplished through the 2-wire DALI connection to the sensor. DALI standard IEC62386_102 Edition 2 defines the logarithmic dimming curve. DALI standard IEC62386_101 Edition 2 defines the linear dimming curve as well as the command for switching between logarithmic and linear curves.






Electrical Specifications

All specifications are typical and at 25°C Ta unless specified otherwise.

Operating Window

The driver current cutback feature provides for an increased output voltage with a reduced output current during abnormal LED operation, such as cold weather starting. Output tolerance +/-5%.




Notes

- 1. Factory default output current is 1.5A.
- 2. To get a 100% to 10% dimming range, the output current setting through AOC should be \geq 1A.
- 3. Factory default minimum dimming level is 10%. This can be adjusted between 10% and 100% using Advance MultiOne.

Electrical Specifications

All specifications are typical and at 25°C Ta unless specified otherwise.


Logic Signal Input (LSI) Characteristics (Typical)



Electrical Specifications

All the specifications are typical and at 25°C Ta unless specified otherwise.


Driver Lifetime Vs. Driver Case Temperature




Performance Characteristics

Based on measurements on a typical sample. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification. Data below at 75°C Tcase.


Efficiency Vs. Output Voltage @ 277VAC



Efficiency Vs. Output Voltage @ 347VAC




Efficiency Vs. Output Voltage @ 480VAC




Performance Characteristics

Based on measurements on a typical sample. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification. Data below at 75°C Tcase.

Power Factor Vs. Output Power




Total Harmonic Distortion Vs. Output Power



Xitanium SR XJ180C180V144VSF2

180W 277-480V 1.8A SR with Auxiliary Supply

Inrush Current Info



Vin	lpeak	T (@ 10% of Ipeak)		
277 Vac	52A	286µs		
480 Vac	91A	289µs		

Inrush current is measured at peak of the corresponding line voltage, source impedance per NEMA 410.

Lightning Surge Info

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)		
Combination Wave (w/t 2 ₂)	6kV	6kV		

Isolation

Isolation	Input Leads	Output Leads	0-10V	Enclosure	
Input Leads	NA	2xU+1kV	2xU+1kV	2xU+1kV	
Output Leads	2xU+1kV	NA	2xU+1kV	2xU+1kV	
SR leads (DA+,DA-/ SGND,Aux and LSI) Class 2 Only	2xU+1kV	2xU+1kV	NA	500V	
Enclosure	2xU+1kV	2xU+1kV	500V	NA	

U = Max. working voltage

(s)ignify

© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9<u>008</u>

All trademarks are owned by Signify Holding or their respective owner