## **ADVANCE**

# by (s) ignify

**LED Driver** 

### Xitanium





XH055C180V054BSY1


Advance Xitanium outdoor LED drivers with SimpleSet technology are designed to give OEMs ultimate flexibility. With the drivers' wide operating windows and simple programming, luminaire manufacturers can design luminaires of different sizes and lumen levels for outdoor applications.

### **Specifications**

Input Volt- age (Vac)	Out- put Power (W)	Out- put Volt- age (V)	Output Cur- rent (A)	Efficiency @ Max. Load and 70°C Case	Max. Case Temp. (°C)	Input Cur- rent (A)	Max. Input Pow- er (W)	THD @ Max. Load (%)	Power Factor @ Max. Load	Surge Pro- tection (Combi- Wave, KV)	Envir. Protection Rating	Dimming	Dimming Range (with specified dimmers)	Mini- mum Output Cur- rent (A)	Driver Type
347		10 54	04.40	88	0000	0.18		100/	0.05		UL damp &	0-10V Analog	10% ~	0.07	Con- stant
480	55	18 - 54	54   0.1 - 1.8	88.5	90°C	0.13	64	<10%	>0.95	6	dry and Type HL	Class 1 and 2 Wiring	100%		Cur- rent


### **Enclosure**

Overall Length (A1)       6.59 (167.5)       ± 0.5         Mounting Length (A2)       6.03 (153.2)       ± 0.5         Case Length (A3)       5.43 (138.0)       ± 0.5         Case Width (B1)       2.31 (58.8)       ± 0.5         Mounting Width (B2)       1.69 (42.9)       ± 0.5         Case Height (C1)       1.48 (37.6)       ± 1.0         Mounting Hole Diameter (D1)       0.31 (7.9)       ± 0.5         Mounting Hole Diameter (D2)       0.24 (6.2)       ± 0.5		In. (mm)	Tolerance (mm)
Case Length (A3)       5.43 (138.0)       ± 0.5         Case Width (B1)       2.31 (58.8)       ± 0.5         Mounting Width (B2)       1.69 (42.9)       ± 0.5         Case Height (C1)       1.48 (37.6)       ± 1.0         Mounting Hole Diameter (D1)       0.31 (7.9)       ± 0.5	Overall Length (A1)	6.59 (167.5)	± 0.5
Case Width (B1) 2.31 (58.8) ± 0.5  Mounting Width (B2) 1.69 (42.9) ± 0.5  Case Height (C1) 1.48 (37.6) ± 1.0  Mounting Hole Diameter (D1) 0.31 (7.9) ± 0.5	Mounting Length (A2)	6.03 (153.2)	± 0.5
Mounting Width (B2)       1.69 (42.9)       ± 0.5         Case Height (C1)       1.48 (37.6)       ± 1.0         Mounting Hole Diameter (D1)       0.31 (7.9)       ± 0.5	Case Length (A3)	5.43 (138.0)	± 0.5
Case Height (C1) 1.48 (37.6) ± 1.0  Mounting Hole Diameter (D1) 0.31 (7.9) ± 0.5	Case Width (B1)	2.31 (58.8)	± 0.5
Mounting Hole Diameter (D1) 0.31 (7.9) ± 0.5	Mounting Width (B2)	1.69 (42.9)	± 0.5
	Case Height (C1)	1.48 (37.6)	± 1.0
Mounting Hole Diameter (D2) 0.24 (6.2) ± 0.5	Mounting Hole Diameter (D1)	0.31 (7.9)	± 0.5
	Mounting Hole Diameter (D2)	0.24 (6.2)	± 0.5
Center of SimpleSet Antenna (G1) 2.30 (58.5) ± 3.0	Center of SimpleSet Antenna (G1)	2.30 (58.5)	± 3.0



### **Wiring Diagram**

	Wire Length (mm)
Black/Orange (Line)	270 (± 30)
Black/White (Neutral)	270 (± 30)
Red (Positive, LED output)	270 (± 30)
Blue (Negative, LED output)	270 (± 30)
Violet (Positive, 0-10V)	270 (± 30)
Pink (Negative, 0-10V)	270 (± 30)



\*DIM- will change from GREY to PINK from 2021 onwards.

#### Warning

- · Install in accordance with national and local electrical codes.
- The field-wiring leads or push-in terminals shall be enclosed.



### 55W 347-480V 0.1-1.8A 0-10V with SimpleSet

#### **Features**

- 50,000+ hour lifetime<sup>1</sup>
- Programmable output current through SimpleSet
- · Large operating window
- 6kV combi-wave surge rating to comply with ANSI C82.77-5 CAT C low

#### **Benefits**

- · Enables long life luminaire designs
- Fast and simple way of programming
- Enables fixture designs with a wide variety of loads and adjustable current options
- No external surge protection required to pass C82.77-5 CAT C low

#### **Application**

- · Area
- · Roadway
- · Parking garages
- Floodlights
- · Mid-bay and low-bay fixtures

### **Electrical Specifications**

All the specifications are typical and at 25°C Ta unless specified otherwise.

#### **Product Data**

Order Information					
Full Product Code	XH055C180V054BSY1M (Mid-Pack, 12pcs/Box), 12NC: 929001711113				
Line Frequency	50/60Hz				
Min. Mains Voltage Operational	312 Vac				
Max. Mains Voltage Operational	528 Vac				
Output Information					
Maximum Open Circuit Voltage	< 60V				
Output Current Ripple (ripple = peak to average / average)	15% max. @ max. lout				
Output Current Tolerance (In the performance window)	<5%				
Protections	Short Circuit, Open Circuit Protection for LED + and LED - and Temperature Foldback				
Features					
0-10V Dimming	150μA (±3%) source current from driver. See dim curve for detail				
AOC (Adjustable Output Current)	0.1A-1.8A via SimpleSet (Factory Default at 1.05A)				
Additional SimpleSet Configurable Features	Adjustable Min Dim level Adjustable Lumen Output Adjustable Lumen Output Min OEM Write Protection Driver Thermal Limit (DTL)				
Environment & Approbation					
Operating Ambient Temp. Range	-40°C to +55°C				
Max. Case Temperature (Tcase)	85°C for life & 90°C for UL				
Agency Approbations	UL 8750, UL Listed, cUL, Class P (UL, cUL)				
Electromagnetic Compliance	FCC Title 47 Part 15 Class A				
Audible Noise	<24dB Class A				
Weight	1.44 Lbs / 0.65 kgs				

Advance Xitanium LED drivers are manufactured to engineering standards correlating to a designed and average life expectancy of 50,000 hours
of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.

### 55W 347-480V 0.1-1.8A 0-10V with SimpleSet

### **Electrical Specifications**


All the specifications are typical and at 25°C Tcase unless specified otherwise.

### 0-10V Dimming Curve

- Dimming source current from the driver: 150µA (@ 0<Vdim<8V)
- Minimum dim level: Factory default 10% of lout (minimum 100mA), can be programmed to a higher level via SimpleSet
- · Maximum output voltage on the dimming wires: 12V
- Leakage current of dimming leads: 0.010mA, recommended max number of control circuits in parallel refer to Design-in Guide

### **Approved Dimmer List**

Manufacturer	Manufacturer Part Number
Lutron	Visit www.lutron.com/ advance for a list of dimmers (Mark VII) that will work with this driver
Leviton	IllumaTech IP7 series
Advance	Sunrise - SR1200ZTUNV




### 55W 347-480V 0.1-1.8A 0-10V with SimpleSet

### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.

### **Driver Output Window**



### **Notes**


- 1. Factory default output current is 1.05A.
- 2. To get a 100% to 10% dimming range, the output current setting through AOC should be > 0.7A.

## 55W 347-480V 0.1-1.8A 0-10V with SimpleSet

### **Electrical Specifications**

All the specifications are typical and at  $25^{\circ}\text{C}$  Ta unless specified otherwise.


### **Output Current Vs. Driver Case Temperature**



### Note

There is ±5°C tolerance on the driver case temperature.

### **Driver Lifetime Vs. Driver Case Temperature**




## 55W 347-480V 0.1-1.8A 0-10V with SimpleSet


### **Performance Characteristics**

Based on measurements on a typical sample at  $75^{\circ}$ C case. The accuracy of the measurements is within the tolerance of the measurement instruments.

### Efficiency Vs. Output Voltage at 347Vac



### Efficiency Vs. Output Voltage at 480Vac




## 55W 347-480V 0.1-1.8A 0-10V with SimpleSet


### **Performance Characteristics**

Based on measurements on a typical sample at  $75^{\circ}$ C case. The accuracy of the measurements is within the tolerance of the measurement instruments.

#### Power Factor Vs. Output Power




### Total Harmonic Distortion (THD) Vs. Output Power



### 55W 347-480V 0.1-1.8A 0-10V with SimpleSet

### **Inrush Current Info**



Vin	Ipeak	T (@ 10% of Ipeak)	
347 Vrms	28A	151µs	
480 Vrms	40A	146µs	

Inrush current is measured at peak of the corresponding line voltage. Source impedance per NEMA 410.

### **Lightning Surge Info**

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)
1.2/50μs Combination Wave (w/t 2Ω)	6kV	6kV

#### Isolation

Isolation	Input	Output	0-10V	Enclosure
Input	NA	2xU+1kV	2.5kV	2xU+1kV
Output	2xU+1kV	NA	2.5kV	500
0-10V	2.5kV	2.5kV	NA	2.5kV
Enclosure	2xU+1kV	500	2.5kV	NA

U = Max. input voltage



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners