




Xitanium Long-lasting and low-maintenance, LED-based light sources are an excellent solution for all outdoor lighting applications. For optimal performance, these solutions require reliable drivers matching the long lifetime of the LEDs. The Advance Xitanium LED outdoor driver portfolio offers a range of products specially designed to operate LED solutions in outdoor applications. These drivers are designed for hard-wired integration into outdoor luminaires for the most rugged applications. They operate to specification under wide temperature and electrical ranges to help ensure reliability.

Specifications


Input Voltage (Vrms)	Output Power (W)	Output Voltage (V)	Output Current (A)	Efficiency@ Max. Load and 70°C Case	Max. Case Temp. (°C)	Input Current (Arms)	Max. Input Power (W)	THD @ Max. Load	Power Factor @ Max. Load	Surge Protection Common/ Diff (KV)	Envir. Protection Rating	Dimming	Dimming Range (with specified dimmers)	Minimum Output Current (A)	Driver Type
120	220	105-163	1.35	91	90°C	2.1	245	<10%	>0.95	6	UL Dry & Damp and Type HL	0-10V Analog Class 1 and 2 Wiring	10% ~ 100%	0.135	Constant Current
277				93		0.9		<15%							

Enclosure

	In. (mm)
Case Length (L2)	9.31 (236.4)
Case Width (W)	2.33 (59.1)
Case Height (H)	1.49 (37.9)
Mounting Length (M)	9.91 (251.6)
Overall Length (L1)	10.47 (265.9)



Wiring Diagram



Warning

- Install in accordance with national and local electrical codes.
- The field-wiring leads or push-in terminals shall be enclosed.

Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V

Features

- 50,000+ hour lifetime¹
- Excellent thermal performance
- 6kV combi-wave surge rating to comply with ANSI C82.77-5 CAT C low
- Efficiency of > 90% over the complete range of operation

Benefits

- Enables long life luminaire designs
- Allows luminaire designs for a wide range of ambient environments
- No external surge protection required to pass C82.77-5 CAT C low
- Enables a high lm/W solution

Application

- Area
- Roadway
- Parking garages
- Floodlights
- High-mast

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Product Data

Order Information	
Full Product Code	XI220C135V163CNA1M (Mid-Pack, 10 pcs/Box) 12NC = 929001753613
Line Frequency	50/60Hz
Min. Mains Voltage Operational	108 Vac
Max. Mains Voltage Operational	305 Vac
Output Information	
Maximum Open Circuit Voltage	330Vdc
Output Current Ripple (ripple = peak to average / average)	15% max @ max Iout
Output Current Tolerance (at maximum output current)	<5%
Protections	Short Circuit, Open Circuit Protection for LED + and LED – and Temperature Foldback
Features	
0-10V Dimming	150µA (±3%) source current from driver. See dim curve for detail.
Environment & Approbation	
Operating Ambient Temp. Range	-40°C to +55°C
Max. Case Temperature (Tcase)	75°C for 100k hours life & 90°C for UL
Agency Approbations	UL 8750, UL Listed, cUL, Class P (UL, cUL)
Electromagnetic Compliance	FCC Title 47 Part 15 Class A
Audible Noise	<24dB Class A
Weight	2.5 Lbs / 1.12 kgs

1. Advance Xitanium LED drivers are manufactured to engineering standards correlating to a designed and average life expectancy of 50,000 hours of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.


Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Driver Operation Window



Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

0-10V Dimming Curve

Dimming source current from the driver: 150µA (@ 0<Vdim<8V)


Minimum dim level: Factory default 10% of Iout

Maximum output voltage on the dimming wires: 12V

The dimming lead leakage current is 0.01mA. The maximum number of drivers that can be connected in parallel to one dimming control circuit is based on this dimming lead leakage current and the calculation is described in the corresponding Design-in Guide.

Approved Dimmer List

Manufacturer	Manufacturer Part Number
Lutron	Visit www.lutron.com/advance for a list of dimmers (Mark VII) that will work with this driver
Leviton	IllumaTech IP7 series
Advance	Sunrise - SR1200ZTUNV




Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.


Output Current Vs. Driver Case Temperature



Note

There is $\pm 5^\circ\text{C}$ tolerance on the driver case temperature.

Driver Lifetime Vs. Driver Case Temperature




Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V

Performance Characteristics

Based on measurements on a typical sample at 70°C Case. The accuracy of the measurements is within the tolerance of the measurement instruments.

Efficiency Vs. Output Voltage




Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V


Performance Characteristics

Based on measurements on a typical sample at 70°C Case. The accuracy of the measurements is within the tolerance of the measurement instruments.

Power Factor Vs. Output Power




Total Harmonic Distortion (THD) Vs. Output Power



Xitanium XI220C135V163CNA1

220W 120-277V 1.35A 0-10V

Inrush Current Info



Vin	Ipeak	T (@ 10% of Ipeak)
120 Vac	97A	253 μ s
277 Vac	231A	215 μ s

Inrush current is measured at peak of the corresponding line voltage, source impedance per NEMA 410.

Lightning Surge Info

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)
1.2/50 μ s Combination Wave (w/t 2 ₂)	6kV	6kV

Isolation

Isolation	Input	Output	0-10V (Class 1 & 2)	Enclosure
Input	NA	2xU+1kV	2.5KVac	2xU+1kV
Output	2xU+1kV	NA	2.5KVac	2xU+1kV
0-10V (Class 1 & 2)	2.5KVac	2.5KVac	NA	2.5KVac
Enclosure	2xU+1kV	2xU+1kV	2.5KVac	NA

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.